


E43100



Climate tube for level sensors

CLIMATIC TUBE L=264



Application

Design	for capacitive level sensors LK, LI
Media	water; water-based media
Medium temperature [°C]	0...65
Pressure rating [bar]	0.5

Operating conditions

Ambient temperature [°C]	20...60
--------------------------	---------

Mechanical data

Weight [g]	86
Material	PP-H; NBR
Length L [mm]	264

Remarks

Pack quantity	1 pcs.
---------------	--------