




Article no longer available - archive entry



Application		
Application	displaying and monitoring analog signals; e.g. pressure sensors, temperature sensors or flow sensors	
Electrical data		
Frequency AC	[Hz]	47...63
Operating voltage	[V]	230 / 115 AC / 24 DC
Current consumption	[mA]	200
Operating conditions		
Ambient temperature	[°C]	0...45
Protection	IP 44; (on the front)	
Mechanical data		
Type of mounting	panel cutout: 91 x 43 mm	
Displays / operating elements		
Display		7-segment LED display, red 6-digit 15 mm
		4 x LED, red
Electrical connection		
Connection		