




Y connection cable

Multicable 1 x Y-Jumper M12

Please see the technical note under "Downloads"



Application		
System		Halogen-free
Electrical data		
Operating voltage	[V]	< 250 AC / < 300 DC
Protection class		II
Max. current load total	[A]	4
Operating conditions		
Ambient temperature	[°C]	-20...90



Y connection cable

Multicable 1 x Y-Jumper M12

Ambient temperature (moving)	[°C]	-20...90
Storage temperature	[°C]	-25...55
Storage humidity	[%]	10...100
Other climatic conditions for storage according to stated class		1K22/ DIN 60721-3-1
Protection		IP 65; IP 67; IP 68; IP 69K

Mechanical data

Weight	[g]	867
Molded-body material		TPU (urethane)
Sealing material		FKM

Remarks


Notes	Please see the technical note under "Downloads"
Pack quantity	1 pcs.

Electrical connection

Cable: 5 m, PUR, Halogen-free, black, Ø 4.3 mm; 3 x 0.34 mm² (42 x Ø 0.1 mm)

Electrical connection - plug

Connection



Electrical connection - Socket

Connector: M12; Moulded body: TPU (urethane), orange; sealing: FKM

Electrical connection - plug


Connector: M12; Moulded body: TPU (urethane), orange



Y connection cable

Multicable 1 x Y-Jumper M12

Diagrams and graphs



Derating I_{max} * 0.8 DIN EN 60512-5-2

X Ambient temperature [°C]

Y Current [A]