




## Connection cable

VDOAF032MSS0002H03STGH030MSS

Please see the technical note under "Downloads"



## Application

System	Free from silicone; Halogen-free; gold-plated contacts; Drag chain suitability
Free from silicone	yes

## Electrical data

Operating voltage [V]	10...36 DC
Protection class	III
Max. current load total [A]	3

## Outputs

Electrical design	PNP
-------------------	-----

## Operating conditions

Ambient temperature [°C]	-25...90
Note on ambient temperature	cULus: ...75
Ambient temperature (moving) [°C]	-25...90
Note on ambient temperature (moving)	cULus: ...75
Protection	IP 65; IP 67; IP 68; IP 69K

## Tests / approvals

MTTF [years]	31710
--------------	-------

## Mechanical data

Weight [g]	76.8
Molded-body material	TPU (urethane)

# EVC228



## Connection cable

VDOAF032MSS0002H03STGH030MSS

Material nut	brass, nickel-plated	
Sealing material	FKM	
Drag chain suitability	yes	
Drag chain suitability	Bending radius for flexible applications	min. 10 x cable diameter
	Travel speed	max. 3.3 m/s for a horizontal travel length of 5 m and max. acceleration of 5 m/s <sup>2</sup>
	Bending cycles	> 5 Mio.
	Torsional strain	± 180 °/m

## Displays / operating elements


Display	Switching status	1 x LED, yellow
	Power	1 x LED, green

## Remarks

Notes	Please see the technical note under "Downloads"	
Pack quantity	1 pcs.	

## Electrical connection - plug


Connector: 1 x M12, straight; coding: A; Moulded body: TPU (urethane), orange; Locking: brass, nickel-plated; Contacts: gold-plated; Tightening torque: 0.6...1.5 Nm



## Electrical connection

Cable: 2 m, PUR, Halogen-free, black, Ø 4.3 mm; 3 x 0.34 mm<sup>2</sup> (42 x Ø 0.1 mm )

## Connection



# EVC228



## Connection cable

VDOAF032MSS0002H03STGH030MSS

### Electrical connection - Socket

Connector: 1 x M8, angled; coding: A; Moulded body: TPU (urethane), black transparent; Locking: brass, nickel-plated; sealing: FKM; Contacts: gold-plated; Tightening torque: 0.3...0.5 Nm

