




Male cordsets

ASTGH040VAS0005P04



| Application | | |
|---|------|--|
| System | | Free from silicone; Halogen-free; gold-plated contacts; Drag chain suitability |
| Application | | sanitary and wet areas in the food industry |
| Free from silicone | | yes |
| Electrical data | | |
| Operating voltage | [V] | < 250 AC / < 300 DC |
| Protection class | | II |
| Max. current load total | [A] | 4 |
| Operating conditions | | |
| Ambient temperature | [°C] | -25...100 |
| Ambient temperature (moving) | [°C] | 0...100 |
| Storage temperature | [°C] | -25...55 |
| Storage humidity | [%] | 10...100 |
| Other climatic conditions for storage according to stated class | | 1K22/ DIN 60721-3-1 |
| Protection | | IP 65; IP 67; IP 68; IP 69K |
| Mechanical data | | |
| Weight | [g] | 168.9 |
| Dimensions | [mm] | 15.5 x 15.5 x 49 |
| Material | | PP Halogen-free |
| Molded-body material | | PP |
| Material nut | | stainless steel (1.4404 / 316L) |

EVF072



Male cordsets

ASTGH040VAS0005P04

| | | |
|------------------------|--|--|
| Drag chain suitability | yes | |
| Drag chain suitability | Bending radius for flexible applications | min. 10 x cable diameter |
| | Travel speed | max. 3.3 m/s for a horizontal travel length of 5 m and max. acceleration of 5 m/s² |
| | Bending cycles | > 1 Mio. |
| | Torsional strain | ± 180 °/m |

Remarks


| | |
|---------------|--------|
| Pack quantity | 1 pcs. |
|---------------|--------|

Electrical connection

Cable: 5 m, MPPE, Halogen-free, grey, Ø 4.9 mm; 4 x 0.34 mm² (42 x Ø 0.1 mm)

Electrical connection - plug

Connector: 1 x M12, straight; coding: A; Moulded body: PP; Locking: stainless steel (1.4404 / 316L); Contacts: gold-plated; Tightening torque: 0.6...1.2 Nm; Take into account the maximum value of the counterpart!



Connection

| | |
|---|----|
| 1 | BN |
| 2 | WH |
| 3 | BU |
| 4 | BK |

| | |
|------|---------------|
| BK = | Core colors : |
| BN = | black |
| BU = | brown |
| WH = | blue |
| | white |