


EVT387



Female cordset

ADOAH040VAS0010G04



Application

| | |
|--------------------|----------------------------------------------------------------------------------|
| System | Free from silicone; gold-plated contacts; screened cable; Drag chain suitability |
| Application | sanitary and wet areas in the food industry |
| Free from silicone | yes |

Electrical data

| | | |
|-----------------------------|-----|-------------------|
| Operating voltage | [V] | < 50 AC / < 60 DC |
| Protection class | | III |
| Max. current load total | [A] | 4 |
| Overall current rating (UL) | [A] | 3 |

Operating conditions

| | | |
|--------------------------------------|------|-----------------------------|
| Ambient temperature | [°C] | -25...100 |
| Note on ambient temperature | | cULus: ...50 |
| Ambient temperature (moving) | [°C] | 5...100 |
| Note on ambient temperature (moving) | | cULus: ...50 |
| Protection | | IP 65; IP 67; IP 68; IP 69K |

Mechanical data

| | | |
|------------------------|------|------------------------------------|
| Weight | [g] | 479.5 |
| Dimensions | [mm] | 26.5 x 15.5 x 36.5 |
| Material | | housing: PVC orange; sealing: EPDM |
| Material nut | | stainless steel (1.4404 / 316L) |
| Drag chain suitability | | yes |

EVT387



Female cordset

ADOAH040VAS0010G04

| | | |
|------------------------|------------------------------------------|------------------------------------------------------------------------------------------------|
| Drag chain suitability | Bending radius for flexible applications | min. 10 x cable diameter |
| | Travel speed | max. 3.3 m/s for a horizontal travel length of 5 m and max. acceleration of 5 m/s ² |
| | Bending cycles | > 1 Mio. |
| | Torsional strain | ± 180 °/m |

Remarks


| | |
|---------------|--------|
| Pack quantity | 1 pcs. |
|---------------|--------|

Electrical connection


Cable: 10 m, PVC, orange, Ø 5.2 mm, screened; 4 x 0.34 mm² (42 x Ø 0.1 mm)

Electrical connection - Socket

Connector: 1 x M12, angled; coding: A; Locking: stainless steel (1.4404 / 316L); Contacts: gold-plated; Tightening torque: 0.6...1.5 Nm; Shielded connection cable: shield not connected



Connection



| | |
|------|---------------|
| | Core colors : |
| BK = | black |
| BN = | brown |
| BU = | blue |
| WH = | white |