



## Inductive sensor

IA-3010-BPOG/20m

Article no longer available - archive entry



## Product characteristics

|                    |               |
|--------------------|---------------|
| Electrical design  | PNP           |
| Output function    | normally open |
| Sensing range [mm] | 10            |
| Housing            | tubular       |
| Dimensions [mm]    | Ø 20          |

## Electrical data

|                             |            |
|-----------------------------|------------|
| Operating voltage [V]       | 10...55 DC |
| Current consumption [mA]    | 7; (24 V)  |
| Protection class            | II         |
| Reverse polarity protection | no         |

## Outputs

|                                                      |               |
|------------------------------------------------------|---------------|
| Electrical design                                    | PNP           |
| Output function                                      | normally open |
| Max. voltage drop switching output DC [V]            | 1             |
| Permanent current rating of switching output DC [mA] | 400           |
| Switching frequency DC [Hz]                          | 100           |
| Short-circuit protection                             | no            |
| Overload protection                                  | no            |

## Monitoring range

|                            |           |
|----------------------------|-----------|
| Sensing range [mm]         | 10        |
| Real sensing range Sr [mm] | 10 ± 10 % |
| Operating distance [mm]    | 0...8.1   |

# IA5018



## Inductive sensor

IA-3010-BPOG/20m

| Accuracy / deviations         |           |                                                                            |              |
|-------------------------------|-----------|----------------------------------------------------------------------------|--------------|
| Correction factor             |           | steel: 1 / stainless steel: 0.7 / brass: 0.4 / aluminum: 0.3 / copper: 0.2 |              |
| Hysteresis                    | [% of Sr] | 1...15                                                                     |              |
| Switch-point drift            | [% of Sr] | -10...10                                                                   |              |
| Operating conditions          |           |                                                                            |              |
| Ambient temperature           |           | [°C]                                                                       | -25...80     |
| Protection                    |           | IP 67                                                                      |              |
| Tests / approvals             |           |                                                                            |              |
| EMC                           |           | EN 60947-5-2                                                               |              |
|                               |           | EN 55011                                                                   | class B      |
| Mechanical data               |           |                                                                            |              |
| Housing                       |           | tubular                                                                    |              |
| Mounting                      |           | non-flush mountable                                                        |              |
| Dimensions                    |           | [mm]                                                                       | Ø 20         |
| Material                      |           | PBT                                                                        |              |
| Displays / operating elements |           |                                                                            |              |
| Display                       |           | Switching status                                                           | 1 x LED, red |
| Accessories                   |           |                                                                            |              |
| Items supplied                |           | Mounting clamp: 1                                                          |              |
| Remarks                       |           |                                                                            |              |
| Pack quantity                 |           | 1 pcs.                                                                     |              |
| Electrical connection         |           |                                                                            |              |
| Cable: 20 m, PVC; 3 x 0.5 mm² |           |                                                                            |              |
| Connection                    |           |                                                                            |              |



Core colors :  
BN = brown  
BU = blue  
BK = black