


IL5018



Inductive sensor

ILA3002-APKG/OBEN/3M/PH RT



Product characteristics		
Electrical design		PNP
Output function		normally closed
Sensing range	[mm]	2
Housing		rectangular
Dimensions	[mm]	40 x 8 x 8
Electrical data		
Operating voltage	[V]	10...36 DC
Current consumption	[mA]	15; (24 V)
Protection class		III
Reverse polarity protection		yes
Outputs		
Electrical design		PNP
Output function		normally closed
Max. voltage drop switching output DC	[V]	2.5
Permanent current rating of switching output DC	[mA]	250
Switching frequency DC	[Hz]	2000
Short-circuit protection		yes
Type of short-circuit protection		yes (non-latching)
Overload protection		yes
Monitoring range		
Sensing range	[mm]	2
Real sensing range Sr	[mm]	2 ± 10 %

IL5018



Inductive sensor

ILA3002-APKG/OBEN/3M/PH RT

Operating distance	[mm]	0...1.62
--------------------	------	----------

Accuracy / deviations

Correction factor		steel: 1 / stainless steel: 0.7 / brass: 0.5 / aluminum: 0.4 / copper: 0.3
Hysteresis	[% of Sr]	1...15
Switch-point drift	[% of Sr]	-10...10

Operating conditions

Ambient temperature	[°C]	-25...70
Protection		IP 65

Tests / approvals

EMC		EN 60947-5-2
MTTF	[years]	3523

Mechanical data

Weight	[g]	56.3
Housing		rectangular
Mounting		flush mountable
Dimensions	[mm]	40 x 8 x 8
Material		brass white bronze coated; LCP
Tightening torque	[Nm]	1; (insertion depth: > 5 mm)

Displays / operating elements

Display	Switching status	1 x LED, red
---------	------------------	--------------


Remarks

Pack quantity		1 pcs.
---------------	--	--------

Electrical connection

Cable: 3 m, PUR; 3 x 0.14 mm²

Connection



BN = Core colors : brown
BU = blue
BK = black