


KG5067



Capacitive sensor

KG-3080NFAKGS2T



- 1 LED ring
- 2 Programming buttons



Product characteristics		
Electrical design		PNP/NPN; (Automatic load detection PNP/NPN)
Output function		normally open / closed; (selectable)
Sensing range	[mm]	8
Communication interface		IO-Link
Housing		Threaded type
Dimensions	[mm]	M18 x 1 / L = 77
Electrical data		
Operating voltage	[V]	10...36 DC
Current consumption	[mA]	< 20
Protection class		II
Reverse polarity protection		yes
Measuring principle		capacitive
Outputs		
Electrical design		PNP/NPN; (Automatic load detection PNP/NPN)
Output function		normally open / closed; (selectable)
Max. voltage drop switching output DC	[V]	2.5
Permanent current rating of switching output DC	[mA]	200
Switching frequency DC	[Hz]	10
Short-circuit proof		yes
Overload protection		yes
Monitoring range		
Sensing range	[mm]	8
Accuracy / deviations		
Hysteresis	[% of Sr]	1...15
Switch-point drift	[% of Sr]	-20...20
Interfaces		
Communication interface		IO-Link
Transmission type		COM1 (4,8 kBaud)

KG5067



Capacitive sensor

KG-3080NFAKGS2T

IO-Link revision	1.1	
SDCI standard	IEC 61131-9 CDV	
Profiles	Smart Sensor	
SIO mode	yes	
Min. process cycle time [ms]	101	
Supported DeviceIDs	Type of operation	DeviceID
	default	387

Operating conditions		
Ambient temperature [°C]	-25...80	
Protection	IP 65; IP 67	

Tests / approvals		
EMC	EN 61000-4-2 ESD	8 kV AD
	EN 61000-4-3 HF radiated	10 V/m
	EN 61000-4-4 Burst	2 kV
	EN 61000-4-6 HF conducted	3 V
	EN 55011	class B
Vibration resistance	EN 60068-2-6 Fc	(10...55 Hz) / 1 mm amplitude, vibration duration 5 min., 30 min. per axis with resonance or 55 Hz
Shock resistance	EN 60068-2-27 Ea	30 g 6 shocks / 11 ms half-sine (x, y, z)
MTTF [years]	560	

Mechanical data		
Weight [g]	96.5	
Housing	Threaded type	
Mounting	non-flush mountable	
Dimensions [mm]	M18 x 1 / L = 77	
Thread designation	M18 x 1	
Material	housing: PP white; sealing: TPE-U; Pushbuttons: TPE-U	

Displays / operating elements		
Display	Switching status	1 x LED, yellow
Teach function	yes	
Electronic lock	yes	

Accessories		
Items supplied	lock nuts: 2	

Remarks		
Pack quantity	1 pcs.	

KG5067





Capacitive sensor

KG-3080NFAKGS2T

Electrical connection

Cable: 2 m, PVC, Ø 4.9 mm; 3 x 0.34 mm²

Connection



BK: OUT / IO-Link
Automatic load detection PNP/NPN
when using a resistive load < 20 kΩ
Core colors :
BK = black
BN = brown
BU = blue