


MK5900



T-slot cylinder sensor

MKI3020-BPKG/A/AS



- 1 fixing element
2 combined head screw for fixing element



Product characteristics

Electrical design	PNP
Output function	normally open
Dimensions [mm]	27.5 x 18 x 15.5

Electrical data

Operating voltage [V]	10...30 DC; (cULus - Class 2 source required)
Current consumption [mA]	< 10
Protection class	III
Reverse polarity protection	yes
Max. power-on delay time [ms]	30

Outputs

Electrical design	PNP
Output function	normally open
Max. voltage drop switching output DC [V]	2.5
Permanent current rating of switching output DC [mA]	100
Switching frequency DC [Hz]	6000
Short-circuit protection	yes
Overload protection	yes

Monitoring range

Magnetic sensitivity [mT]	2
---------------------------	---

MK5900



T-slot cylinder sensor

MKI3020-BPKG/A/AS

Travel speed	[m/s]	> 10
--------------	-------	------

Accuracy / deviations

Hysteresis	[mm]	< 1
------------	------	-----

Repeatability	[mm]	< 0.2
---------------	------	-------

Operating conditions

Ambient temperature	[°C]	-25...85
---------------------	------	----------

Protection		IP 65; IP 67
------------	--	--------------

Tests / approvals

EMC	EN 61000-4-2 ESD	- CD / 8 kV AD
	EN 61000-4-3 HF radiated	10 V/m
	EN 61000-4-4 Burst	2 kV
	EN 61000-4-6 HF conducted	10 V
	EN 55011	class B

MTTF	[years]	1887
------	---------	------

Mechanical data

Weight	[g]	12.4
--------	-----	------

Mounting		non-flush mountable
----------	--	---------------------

Type of mounting		fixing element with combined head slot / hexagon socket AF 1.5
------------------	--	--

Cylinder type		T-slot cylinders
---------------	--	------------------

Dimensions	[mm]	27.5 x 18 x 15.5
------------	------	------------------

Material		housing: PA; fixing element: stainless steel / brass
----------	--	--

Displays / operating elements

Display	Switching status	1 x LED, yellow
---------	------------------	-----------------

Accessories

Items supplied		rubber memory stop: 1
----------------	--	-----------------------

Remarks

Pack quantity		1 pcs.
---------------	--	--------

Electrical connection - plug

Connector: 1 x M8; coding: A; Locking: snap-fit



MK5900

T-slot cylinder sensor

MKI3020-BPKG/A/AS



Connection

