




Safety light grids

OYA0810-03-4-60-P-1

For 8-wire cordsets the core colors are not standardized.
Please note the wiring of the sensor and the cordsets (see data sheet).



- T transmitter
- R receiver
- 1 LED red
- 2 LED green
- 3 LED yellow
- 4 LED orange
- 5 LED red
- 6 LED green
- 7 LED yellow
- 8 LED yellow
- 9 LED yellow
- 10 display
- 11 LED orange





Safety light grids

OYA0810-03-4-60-P-1

Product characteristics		
Type of light	Infrared light	
Electrical design	PNP	
Protection	IP 65	
Application		
Protective function	Access prevention body protection	
Electrical data		
Operating voltage tolerance	[%]	20
Operating voltage	[V]	24 DC
Protection class		III
Reverse polarity protection		yes
Power-on delay time	[s]	< 10
Type of light	Infrared light	
Wave length	[nm]	950
Receiver		
Current consumption	[mA]	250
Transmitter		
Current consumption	[mA]	125
Outputs		
Electrical design	PNP	
Number of OSSD outputs	2	
Max. current load per OSSD output	[mA]	500; (24 V)
Short-circuit protection	yes	
Monitoring range		
Protected area height	[mm]	810
Number of beams	3	
Protection area width (low light intensity)	[m]	8...30
Protection area width (high light intensity)	[m]	18...60
Reaction times		
Response time	[ms]	7
Operating conditions		
Applications	Class C to EN 60654-1 weatherproof application	
Ambient temperature	[°C]	-10...55
Max. relative air humidity	[%]	95
Protection	IP 65	
Tests / approvals		
EMC	IEC 61496-1	
Shock resistance	IEC 61496-1	
Vibration resistance	IEC 61496-1	
Safety classification		
ESPE type (IEC 61496-1)	4	



Safety light grids

OYA0810-03-4-60-P-1

Complies with the requirements	ISO 13849-1: 2015 Category 4, PL e	
	IEC 61508 SIL 3	
	IEC 62061 SIL 3	
Mission time TM	[h]	175200
PFH	[1/h]	7,7E-09

Mechanical data

Weight	[g]	6910
Dimensions	[mm]	1036 x 50 x 60
Material	housing: aluminum; front lens: PC	
Length L	[mm]	1036

Displays / operating elements

Display	transmitter	4 x LED
	receiver	6 x LED
	receiver	LC display


Accessories

Items supplied	Assembly angle: 6
	Slot nuts: 6

Remarks

Pack quantity	1 pcs.
---------------	--------


Electrical connection - receiver

Connector: 1 x M12; coding: A; Maximum cable length: 100 m; for wire cross-section 1 mm²

Safety light grids


OYA0810-03-4-60-P-1

Connection



Electrical connection - transmitter

Connector: 1 x M12; coding: A



Connection

