
PS4408

Hydrostatic submersible pressure transmitter

SUBMERSIBLE 0,25BAR 10M FEP CABLE





C€ CA

Product characteristics		-	_	_		-
Number of inputs and outpu	its		N	lumber of analog ou	utputs: 1	
Measuring range		00.25 bar	0250 mbar	03.63 psi	0100.4 inH2O	025 kPa
Application						
Design			with capil	ary tube for pressu	re compensation	
Application				for industrial applic	ations	
Media				Liquids		
Medium temperature	[°C]			-1085		
Min. bursting pressure		2.4 bar	35	i psi	240 kPa	
Pressure rating		2 bar	29	psi	200 kPa	
Type of pressure				relative pressu	re	
Electrical data						
Operating voltage	[V]			1030 DC		
Protection class				III		
Reverse polarity protection				yes		
Measuring principle				hydrostatic		
Inputs / outputs						
Number of inputs and output	its	Number of analog outputs: 1				
Outputs						
Total number of outputs				1		
Output signal		analog signal				
Number of analog outputs		1				
Analog current output	[mA]	420				
Max. load	[Ω]		700;	(Ub = 24 V; (Ub - 10) V) / 20 mA)	
Short-circuit protection			,	yes	,	
Measuring/setting range						
Measuring range		00.25 bar	0250 mbar	03.63 psi	0100.4 inH2O	025 kPa
Accuracy / deviations			,			
	ne span]		< 0,1; (w	ith temperature fluc	tuations < 10 K)	
Characteristics deviation [% of the content of the	ne span]	< 0,25 (BFSL) / 0,5; (incl. linearity, zero and span error (limit value setting))				
Linearity deviation [% of the	ne span]			< 0,2 (BFSL)		
Long-term stability [% of the	ne span]			< 0,2; (per yea	ar)	

PS4408

Hydrostatic submersible pressure transmitter



SUBMERSIBLE 0,25BAR 10M FEP CABLE

Temperature coefficient zero point [% of the span / 10 K]	< ± 0,2; (050 °C)
Temperature coefficient span [% of the span / 10 K]	<±0,2; (050 °C)

Operating conditions		
Ambient temperature	[°C]	-1085
Storage temperature	[°C]	-3080
Protection		IP 68

Tests / approvals		
MTTF	[years]	403
Pressure equipment directive		sound engineering practice; can be used for group 2 fluids; group 1 fluids on request


Mechanical data		
Weight	[g]	991.5
Material		stainless steel (1.4571/316Ti); PA
Remarks		

Pack quantity 1 pcs.	Remarks	
	Pack quantity	1 pcs.

Electrical connection

Cable: 10 m, FEP, Ø 7.5 mm

Connection



1: screen (connected to the housing)

Core colors:

BN = brown GN = green