
## PS4607

## Hydrostatic submersible pressure transmitter



SUBMERSIBLE 1BAR 30M FEP CABLE



<b>Product characteristics</b>	i					
Number of inputs and outputs		Number of analog outputs: 1				
Measuring range		01 bar	01000 mbar	014.5 psi	0401.5 inH2O	0100 kPa
Application						
Design			with capilla	ry tube for pressure	e compensation	
Application		for industrial applications				
Media		Liquids				
Medium temperature	[°C]	-1085				
Min. bursting pressure		6 bar	87 p	osi	600 kPa	
Pressure rating		5 bar	72.5	5 psi	500 kPa	
Type of pressure				relative pressur	e	
Electrical data						
Operating voltage	[V]			1030 DC		
Protection class				111		
Reverse polarity protection	on			yes		
Measuring principle				hydrostatic		
Inputs / outputs						
Number of inputs and outputs		Number of analog outputs: 1				
Outputs						
Total number of outputs				1		
Output signal				analog signal		
Number of analog outputs		1				
Analog current output	[mA]			420		
Max. load	[Ω]	700; (Ub = 24 V; (Ub - 10 V) / 20 mA)				
Short-circuit protection				yes		
Measuring/setting rang	е					
Measuring range		01 bar	01000 mbar	014.5 psi	0401.5 inH2O	0100 kPa
Accuracy / deviations						
Repeatability [% c	of the span]		< 0,1; (wit	h temperature fluct	tuations < 10 K)	
Characteristics deviation [% of the span]		< 0,25 (BFSL) / 0,5; (incl. linearity, zero and span error (limit value setting))				
Linearity deviation [% of the span]		< 0,2 (BFSL)				
Long-term stability [% c	of the span]			< 0,2; (per yea	r)	


## PS4607

## Hydrostatic submersible pressure transmitter

SUBMERSIBLE 1BAR 30M FEP CABLE



Temperature coefficient zero point [% of the span / 10 K]		< ± 0,2; (050 °C)		
Temperature coefficient span [% of the span / 10 K]		< ± 0,2; (050 °C)		
Operating conditions				
Ambient temperature	[°C]	-1085		
Storage temperature	[°C]	-3080		
Protection		IP 68		
Tests / approvals				
MTTF	[years]	403		
Pressure equipment directive		sound engineering practice; can be used for group 2 fluids; group 1 fluids on request		
Mechanical data				
Weight	[g]	2376		
Material		stainless steel (1.4571/316Ti ); PA		
Remarks				
Pack quantity		1 pcs.		
Electrical connection				
Cable: 30 m, FEP, Ø 7.5 m	ım			
Connection				



1:	screen (connected to the housing) Core colors :
BN =	brown
GN =	green