


## Licence for the software for intelligent monitoring and optimization of manufacturing processes

moneo DataScience Starter LIC

# moneo|DataScience Toolbox



Application	
Application	moneo RTM add-on for dynamic condition monitoring of machines, plants and wear components using AI methods
Configuration	configuration of dynamic thresholds user-dependent setting of the warning and the alarm function
Compatibility	compatible with IO-Link to current specification of the IO-Link Community
Connectivity	IO-Link masters and devices VSE diagnostic electronics for vibration sensors
Monitoring	permanent monitoring of target variables by means of calculating dynamic expectation ranges automated ticket creation when dynamic thresholds are reached
User interface	5-step wizard for configuring the dynamic warning and alarm thresholds live display of the sensor values and the dynamic warning and alarm thresholds



## Licence for the software for intelligent monitoring and optimization of manufacturing processes

moneo DataScience Starter LIC

Software / programming	
Language	German; English; French; Italian; Spanish; Portuguese; Chinese; Japanese; Korean; Russian
Data carrier	download
Type of license	single license
License class	full version
System requirements	
Min. CPU cycle	2,3 GHz
Min. number of CPU cores	4
Min. RAM	8
Min. graphic resolution	1920 x 1080
Required device interface	USB; LAN Adapter - RJ45
Network card	Ethernet 1 Gbit
Network protocol	Ethernet TCP/IP
Operating system	Microsoft Windows 10 64 Bit; Microsoft Windows Server 2016; Microsoft Windows Server 2019; Microsoft Windows Server 20H2
Web browser	Google Chrome; Mozilla Firefox; (supported versions: see current release notes)
Additionally required software	moneo software download
	moneo OS License
	moneo RTM License
	moneo edgeConnect
	moneo infopoints