

U10003

Mounting adapter for capacitive sensors







Application		
Design		for types M30
Pressure rating	[bar]	6.9
Operating conditions		
Ambient temperature	[°C]	-25246
Note on ambient temperate	ure	-25260 for short duration
Mechanical data		
Weight	[g]	90.718
Material		PTFE
Process connection		1 1/4" NPT
Remarks		
Pack quantity		1 pcs.