



AS-Interface gateway

BACKPLANE MASTER-COMPACTLOGIX

No scale drawing available

Application		
Application	ASI master for Compactlogix and Micrologix 1500 PLC platforms	
Electrical data		
Operating voltage	[V]	30 DC; (AS-i)
Current consumption	[mA]	5 V DC: 450 mA; AS-i: 100 mA
Number of AS-i masters	1	
Interfaces		
Communication interface	RS232	
RS232		
Number of R232 interfaces	1	
Transmission rate	9600...115200 Baud	
Type of connector	RJ11	
Usage type	Programming	
Operating conditions		
Ambient temperature	[°C]	0...55
Storage temperature	[°C]	-25...85
Protection	IP 20	
AS-i classification		
AS-i version	3.0	
Mechanical data		
Weight	[g]	226.796
Displays / operating elements		
Display	LED display	
Remarks		
Remarks	Configuration is handled through Allen-Bradleys' RSLogix software.	
Pack quantity	1 pcs.	