

E10699



Connecting cable with socket

ADOAH050MSS0005B05

Article no longer available - archive entry

Alternative articles: EVC074
When selecting an alternative article and accessories please note that technical data may differ!



Electrical data		
Operating voltage	[V]	< 30 AC / < 36 DC
Operating conditions		
Ambient temperature	[°C]	-25...90
Protection		IP 67
Mechanical data		
Dimensions	[mm]	27 x 15 x 39
Materials		TPU
Moulded-body material		TPU
Material nut		brass, nickel-plated
Remarks		
Pack quantity		1 pcs.

E10699



Connecting cable with socket


ADOAH050MSS0005B05

Electrical connection


Cable: 5 m, PUR, black; 5 x 0.5 mm² (16 x Ø 0.2 mm)

Electrical connection - socket

Connector: 1 x M12, angled; coding: A; Moulded body: TPU; Locking: brass, nickel-plated



Connection



	Core colours :
BK =	black
BN =	brown
BU =	blue
GY =	grey
WH =	white