

# E11076



## Connecting cable with socket

ADOGB050MSS0002E05



### Electrical data

|                         |     |             |
|-------------------------|-----|-------------|
| Operating voltage       | [V] | < 300 AC/DC |
| Max. current load total | [A] | 4           |

### Operating conditions

|                              |      |          |
|------------------------------|------|----------|
| Ambient temperature          | [°C] | -30...80 |
| Ambient temperature (moving) | [°C] | -5...80  |
| Protection                   |      | IP 68    |

### Mechanical data

|                       |      |                |
|-----------------------|------|----------------|
| Weight                | [g]  | 137.7          |
| Dimensions            | [mm] | 26 x 26 x 49.9 |
| Moulded-body material |      | TPU            |
| Material nut          |      | diecast zinc   |

### Remarks

|               |  |        |
|---------------|--|--------|
| Pack quantity |  | 1 pcs. |
|---------------|--|--------|

# E11076



## Connecting cable with socket

ADOGB050MSS0002E05

### Electrical connection

Cable: 2 m, PVC, black; 5 x 0.5 mm<sup>2</sup> (16 x Ø 0.2 mm )

### Electrical connection - socket

Connector: 1 x 7/8", straight; Moulded body: TPU; Locking: diecast zinc



### Connection

|   |       |
|---|-------|
| 1 | BK    |
| 2 | BU    |
| 3 | GN/YE |
| 4 | BN    |
| 5 | WH    |

|         |                |
|---------|----------------|
|         | Core colours : |
| BK =    | black          |
| BN =    | brown          |
| BU =    | blue           |
| GN/YE = | green/yellow   |
| WH =    | white          |