


## Inductive sensor

IIA2010-FRKG/PH



## Product characteristics

|                    |                                               |
|--------------------|-----------------------------------------------|
| Electrical design  | PNP/NPN                                       |
| Output function    | normally open / normally closed; (selectable) |
| Sensing range [mm] | 10                                            |
| Housing            | threaded type                                 |
| Dimensions [mm]    | M30 x 1.5 / L = 81                            |

## Electrical data

|                             |            |
|-----------------------------|------------|
| Operating voltage [V]       | 10...55 DC |
| Protection class            | II         |
| Reverse polarity protection | yes        |

## Outputs

|                                                      |                                               |
|------------------------------------------------------|-----------------------------------------------|
| Electrical design                                    | PNP/NPN                                       |
| Output function                                      | normally open / normally closed; (selectable) |
| Max. voltage drop switching output DC [V]            | 4.6                                           |
| Minimum load current [mA]                            | 4                                             |
| Max. leakage current [mA]                            | 0.5                                           |
| Permanent current rating of switching output DC [mA] | 400                                           |
| Switching frequency DC [Hz]                          | 450                                           |
| Short-circuit protection                             | yes                                           |
| Type of short-circuit protection                     | pulsed                                        |
| Overload protection                                  | yes                                           |

## Detection zone

|                               |                |
|-------------------------------|----------------|
| Sensing range [mm]            | 10             |
| Real sensing range $S_r$ [mm] | $10 \pm 10 \%$ |
| Operating distance [mm]       | 0...8.1        |

## Accuracy / deviations

|                   |                                                                             |
|-------------------|-----------------------------------------------------------------------------|
| Correction factor | steel: 1 / stainless steel: 0.7 / brass: 0.4 / aluminium: 0.3 / copper: 0.2 |
|-------------------|-----------------------------------------------------------------------------|



Inductive sensor

IIA2010-FRKG/PH

|                    |           |          |
|--------------------|-----------|----------|
| Hysteresis         | [% of Sr] | 1...15   |
| Switch point drift | [% of Sr] | -10...10 |

Operating conditions

|                     |      |          |
|---------------------|------|----------|
| Ambient temperature | [°C] | -25...80 |
| Protection          |      | IP 67    |

Tests / approvals

|      |              |         |
|------|--------------|---------|
| EMC  | EN 60947-5-2 |         |
|      | EN 55011     | class B |
| MTTF | [years]      | 1835    |

Mechanical data

|                    |      |                          |
|--------------------|------|--------------------------|
| Weight             | [g]  | 264                      |
| Housing            |      | threaded type            |
| Mounting           |      | flush mountable          |
| Dimensions         | [mm] | M30 x 1.5 / L = 81       |
| Thread designation |      | M30 x 1.5                |
| Materials          |      | brass nickel-plated; PBT |

Displays / operating elements

|         |                  |              |
|---------|------------------|--------------|
| Display | switching status | 1 x LED, red |
|---------|------------------|--------------|

Accessories

|                |              |
|----------------|--------------|
| Items supplied | lock nuts: 2 |
|----------------|--------------|



Remarks

|               |        |
|---------------|--------|
| Pack quantity | 1 pcs. |
|---------------|--------|

Electrical connection

Cable: 2 m, PUR / PVC; 2 x 0.5 mm²

Connection



Core colours :  
BK = black  
WH = white