



Fibre optic diffuse reflection sensor

FT-00-M-V-R4/1m

Article no longer available - archive entry

Alternative articles: E20495

When selecting an alternative article and accessories please note that technical data may differ!

No scale drawing available

Application

Function principle	Diffuse reflection sensor
--------------------	---------------------------

Detection zone

Range with fibre optic amplifier type	OKF; OUF
---------------------------------------	----------

OKF

Range fibre optics [mm]	40
-------------------------	----

OUF

Range fibre optics [mm]	40
-------------------------	----

Operating conditions

Ambient temperature [°C]	-20...150
--------------------------	-----------

Mechanical data

Version of sensing head	angled
Total length [mm]	1000
Min. bending radius [mm]	20
Fibre material	glass
Fibre head material	stainless steel (1.4305 / 303)
Fibre sheath material	metal silicone

Remarks

Pack quantity	1 pcs.
---------------	--------