
# E12228

## Connecting cable with socket

ADOAH040VAS0010G04

Article no longer available - archive entry




| | | |
|---|---|---|
| **Application** | | |
| Special feature | | Free from silicone; Gold-plated contacts; Screened cable |
| Free from silicone | | yes |
| **Electrical data** | | |
| Operating voltage | [V] | < 50 AC / < 60 DC |
| Protection class | | III |
| Max. current load total | [A] | 4 |
| **Operating conditions** | | |
| Ambient temperature | [°C] | -25...100 |
| Protection | | IP 67 |
| **Mechanical data** | | |
| Weight | [g] | 506.4 |
| Dimensions | [mm] | 26.5 x 15 x 38.5 |
| Materials | | PVC |
| Moulded-body material | | PVC |
| Material nut | | stainless steel (1.4404 / 316L) |
| **Remarks** | | |
| Pack quantity | | 1 pcs. |

# E12228

## Connecting cable with socket

**ADOAH040VAS0010G04**

### Electrical connection


Cable: 10 m, PVC, orange, Ø 5.3 mm, shielded; 4 x 0.34 mm² (42 x Ø 0.1 mm )

### Electrical connection - socket

Connector: 1 x M12, angled; coding: A; Moulded body: PVC; Locking: stainless steel (1.4404 / 316L); Contacts: gold-plated; Tightening torque: 0.7...0.9 Nm; Shielded connection cable: screen not connected




### Connection




| | Core colours : |
|---|---|
| BK = | black |
| BN = | brown |
| BU = | blue |
| WH = | white |