
E33071

Mounting adapter for process sensors

ADAPT IFM-SMS DN40(1.5)GWD

Article no longer available - archive entry



1 Aseptoflex thread
2 Aseptoflex sealing edge

Application		
Pressure rating	[bar]	25
Tests / approvals		
Pressure Equipment Directive		A possible classification to PED depends on the application and has to be carried out by the user / operator.
Safety instructions		The compatibility between medium and product material has to be checked in all applications.
Mechanical data		
Materials		stainless steel (1.4404 / 316L)
Sensor connection		Aseptoflex
Process connection		flange DN40 (1,5")
Surface characteristics Ra/Rz of the wetted parts		0.4 / 4
Hygienic equipment class to DIN 11866		H4
Remarks		
Pack quantity		1 pcs.