
# E43344

## Process adapter for SMS pipe fitting

ADAPT G1/2 - SMS DN50/2"




1 sealing edge

EC 1935/2004 FCM

| | | |
|---|---|---|
| **Application** | | |
| Design | | with leakage port |
| Pressure rating | [bar] | 16 |
| **Tests / approvals** | | |
| Pressure Equipment Directive | | A possible classification to PED depends on the application and has to be carried out by the user / operator. |
| Safety instructions | | The compatibility between medium and product material has to be checked in all applications. |
| **Mechanical data** | | |
| Weight | [g] | 570.5 |
| Materials | | stainless steel (1.4435 / 316L) |
| Sensor connection | | G 1/2 sealing cone |
| Process connection | | SMS pipe fitting DN50 (2") |
| Surface characteristics Ra/Rz of the wetted parts | | < 0.8 / 8 |
| Sealing | | metal to PEEK |

# E43344

## Process adapter for SMS pipe fitting

ADAPT G1/2 - SMS DN50/2"

| | |
|---|---|
| Hygienic equipment class to DIN 11866 | H3 |
| **Remarks** | |
| Pack quantity | 1 pcs. |