
E20993

Reflector for retro-reflective laser sensors

REFLECTOR LASER TS-19



1 M3 8 mm deep

Application		
Design		round, for retro-reflective laser sensors, M3
Operating conditions		
Ambient temperature	[°C]	-10...60
Mechanical data		
Weight	[g]	3
Dimensions	[mm]	Ø 19 / L = 5
Reflector surface	[mm]	Ø 17
Materials		screw: stainless steel (316 / 1.4401); Spring washer: stainless steel (316 / 1.4401); nut: stainless steel (316 / 1.4401); front panel: PMMA; base: ABS
Remarks		
Pack quantity		1 pcs.