
E18423

Connection cable

VDOGH040MSS0010X04GXS



Application		
Design		Ethernet cable, D-coded
Application		cross-over patch cable; patch cable
Operating conditions		
Ambient temperature	[°C]	-25...70
Protection		IP 67; IP 42; (M12 plug / RJ45 plug)
Mechanical data		
Weight	[g]	703.068
Materials		PUR / PC
Moulded-body material		PUR / PC
Material nut		brass, nickel-plated
Remarks		
Pack quantity		1 pcs.

Electrical connection - plug M12

Connector: 1 x M12, straight; coding: D; Moulded body: PUR; Locking: brass, nickel-plated; Tightening torque: 0.7...0.9 Nm



E18423


Connection cable

VDOGH040MSS0010X04GXS

Electrical connection

Cable: 10 m, PUR, green, Ø 6.2 mm; 2 x 0.38 mm²

Connection



Electrical connection - plug RJ45

Connector: 1 x RJ45, straight; Moulded body: PC

