
E18535

Adapter socket

RDOGF030MSS0001-03



1 O-ring

Electrical data		
Operating voltage	[V]	< 60 AC / < 75 DC
Protection class		III
Max. current load total	[A]	4
Operating conditions		
Ambient temperature	[°C]	-25...80
Protection		IP 67
Mechanical data		
Weight	[g]	20.865
Mounting thread		M8
Materials		brass nickel-plated
Moulded-body material		brass, nickel-plated
Remarks		
Pack quantity		1 pcs.

E18535

Adapter socket


RDOGF030MSS0001-03

Electrical connection


Cable: 0.15 m, PVC; 2 x 0.34 mm²

Electrical connection - socket

Connector: 1 x M8; coding: A; Moulded body: brass, nickel-plated



Connection



	Core colours :
BN =	brown
BU =	blue