
E20435

Fibre optic diffuse reflection sensor

FT-00-A-V-E1/0,35m

Article no longer available - archive entry



Application		
Function principle		Diffuse reflection sensor
Detection zone		
Range with fibre optic amplifier type		OKF; OUF
OKF		
Range fibre optics	[mm]	8
OUF		
Range fibre optics	[mm]	8
Operating conditions		
Ambient temperature	[°C]	-40...290
Mechanical data		
Version of sensing head		straight
Sensing head diameter	[mm]	1
Sensing head length	[mm]	5
Total length	[mm]	350; (+5 mm)
Min. bending radius	[mm]	20
Materials		Adapter: ABS
Fibre material		glass

E20435

Fibre optic diffuse reflection sensor

FT-00-A-V-E1/0,35m

Fibre head material	stainless steel (1.4305 / 303)
Fibre sheath material	aluminium
Remarks	
Pack quantity	1 pcs.