
E20238

Fibre optic through-beam sensor

FE-00-A-A-R3/1M

Article no longer available - archive entry

Alternative articles: E20364
When selecting an alternative article and accessories please note that technical data may differ!



Application		
Function principle		Through-beam sensor
Detection zone		
Range with fibre-optic amplifier type		OKF; OUF
OKF		
Range of fibre optics	[mm]	120
OUF		
Range of fibre optics	[mm]	120
Operating conditions		
Ambient temperature	[°C]	-40...290
Mechanical data		
Version of sensing head		angled
Sensing head diameter	[mm]	3
Sensing head length	[mm]	10
Total length	[mm]	1000

E20238

Fibre optic through-beam sensor

FE-00-A-A-R3/1M

Min. bending radius	[mm]	20
Materials		Adapter: ABS
Fibre material		glass
Fibre head material		aluminium
Fibre sheath material		aluminium
Remarks		
Pack quantity		1 pcs.