
E30144

Clamp fitting for process sensors

G 1/2" COMPRESSION FITTING



1 clamping screw
2 clamping ring
3 screw-in adapter

EC 1935/2004 **EHEDG** Tested FDA

Application		
Application		hygienic systems
Installation		Clamp fitting
Recommended media		viscous media and liquids with suspended particles
Pressure rating	[bar]	10
No dead space		yes
Operating conditions		
Ambient temperature	[°C]	-10...150
Tests / approvals		
Pressure Equipment Directive		A possible classification to PED depends on the application and has to be carried out by the user / operator.
Safety instructions		The compatibility between medium and product material has to be checked in all applications.
Mechanical data		
Weight	[g]	102.8
Materials		stainless steel (1.4404 / 316L); clamping ring: PEEK
Tightening torque	[Nm]	< 10
Sensor connection		Ø 6 mm
Process connection		threaded connection G 1/2 sealing cone

E30144

Clamp fitting for process sensors

G 1/2" COMPRESSION FITTING

Surface characteristics Ra/Rz of the wetted parts	Ra: < 0.8

Remarks	
Pack quantity	1 pcs.