
# E33211

## Process adapter hygienic pipe fitting

ADAPT IFM-DIN11851 DN32/1.25"




1 Aseptoflex Vario
2 sealing area

EC 1935/2004 FDA

| | | |
|---|---|---|
| **Application** | | |
| Pressure rating | [bar] | 40 |
| **Tests / approvals** | | |
| Pressure Equipment Directive | | A possible classification to PED depends on the application and has to be carried out by the user / operator. |
| Safety instructions | | The compatibility between medium and product material has to be checked in all applications. |
| **Mechanical data** | | |
| Weight | [g] | 134 |
| Materials (wetted parts) | | stainless steel (1.4435 / 316L) ; surface characteristics : Ra<0,4 / Rz 4 |
| Sensor connection | | G 1 internal thread Aseptoflex Vario |
| Process connection | | hygienic pipe fitting DN32 (1,25") DIN 11851 |
| Sealing | | Gasket |
| Hygienic equipment class to DIN 11866 | | H4 |
| **Accessories** | | |
| Items supplied | | O-ring: 1 x 24 x 2, EPDM, FDA compliant, E30054 |
| Accessories (optional) | | O-ring: 1 x 24 x 2, FKM, FDA compliant, E30123 |
| | | sealing ring: 1, PEEK, FDA compliant, E30124 |
| **Remarks** | | |
| Pack quantity | | 1 pcs. |