
E33340

Universal process adapter

ADAPT UNI RD52



1 O-ring 38 x 2 (FKM) FDA compliant
2 O-ring 36 x 3 (EPDM) FDA compliant
3 sealing area
4 Aseptoflex Vario

EC 1935/2004 FDA

Application		
Pressure rating	[bar]	16
Tests / approvals		
Pressure Equipment Directive		A possible classification to PED depends on the application and has to be carried out by the user / operator.
Safety instructions		The compatibility between medium and product material has to be checked in all applications.

E33340

Universal process adapter

ADAPT UNI RD52

Mechanical data		
Weight	[g]	364.5
Materials (wetted parts)		stainless steel (1.4435 / 316L) ; surface characteristics : Ra<0,4 / Rz 4
Sensor connection		G 1 internal thread Aseptoflex Vario
Process connection		universal process adapter Rd 52
Sealing		Gasket
Hygienic equipment class to DIN 11866		H4
Accessories		
Items supplied		O-ring: 24 x 2, EPDM, FDA compliant, E30054
		O-ring: 38 x 2, FKM
		O-ring: 36 x 3, EPDM, FDA compliant
Accessories (optional)		O-ring: 24 x 2, FKM, FDA compliant, E30123
		sealing ring, PEEK, FDA compliant, E30124
Remarks		
Pack quantity		1 pcs.