
W80110

Connecting cable with socket

ADOGA030MKS0005E03




Electrical data		
Operating voltage	[V]	< 300 AC/DC
Operating conditions		
Ambient temperature	[°C]	-20...105
Protection		IP 68
Mechanical data		
Weight	[g]	226.796
Dimensions	[mm]	14.5 x 14.5 x 46.7
Materials		PVC
Moulded-body material		PVC
Material nut		zinc, epoxy coated
Remarks		
Pack quantity		1 pcs.

Electrical connection

Cable: 4.57 m, PVC, yellow, Ø 5.84 mm; 3 x 0.34 mm² / AWG 22

Electrical connection - socket

Connector: 1 x 1/2", straight; coding: C; Moulded body: PVC; Locking: zinc, epoxy coated




W80110

Connecting cable with socket

ADOGA030MKS0005E03

Connection



	Core colours :
GN =	green
RD/BK =	red/black
RD/WH =	red/white