
CR1085

Programmable graphic display for controlling mobile machines

R360/PDM NG/DialogDisplay/C



Electrical data		
Operating voltage	[V]	10...32 DC
Power consumption	[W]	7.2
Inputs / outputs		
Number of inputs and outputs		Number of digital inputs: 1; Number of analogue inputs: 1; Number of digital outputs: 1
Inputs		
Number of digital inputs		1
Number of analogue inputs		1
Analogue input (current)	[mA]	0...20
Analogue input (voltage)	[V]	0...32
Outputs		
Number of digital outputs		1
Software / programming		
PLC function to IEC 61131-3		yes
Interfaces		
Number of CAN interfaces		4
Number of Ethernet interfaces		1
Number of USB interfaces		2
Number of video interfaces (CVBS)		2
Mechanical data		
Weight	[g]	1669

CR1085

Programmable graphic display for controlling mobile machines

R360/PDM NG/DialogDisplay/C

Type of mounting		panel / surface	
Dimensions	[mm]	146 x 225 x 64.5	
Displays / operating elements			
Display			7" colour display
Operating elements		9	freely programmable backlit function keys
		1	navigation key with pushbutton
Display resolution		800 x 480	
Display type		colour display	
Display size		7"	
Display background illumination		LED	
Data memories			
Real-time clock		yes	
Remarks			
Pack quantity		1 pcs.	
Electrical connection			

Connector: 1 x M12