
E70145

Jumper cable with valve plug

VVDAB031--S00,6A03STAH030VAS

Article no longer available - archive entry



Application		
Special feature		Halogen-free
Electrical data		
Operating voltage	[V]	< 24 AC/DC
Operating conditions		
Ambient temperature	[°C]	-25...90
Protection		IP 67
Mechanical data		
Dimensions	[mm]	30 x 15 x 39
Materials		PUR
Moulded-body material		PUR
Material nut		stainless steel (1.4404 / 316L)
Displays / operating elements		
Display	switching status	1 x LED, yellow
Accessories		
Items supplied		screw
		panel for labelling

E70145

Jumper cable with valve plug


VVDAB031--S00,6A03STAH030VAS

Remarks

Pack quantity	1 pcs.

Electrical connection - plug


Connector: 1 x M12, angled; coding: A; Moulded body: PUR; Locking: stainless steel (1.4404 / 316L)



Electrical connection

Cable: 0.6 m, PUR, Halogen-free, black, Ø 5.5 mm; 3 x 0.5 mm² (16 x Ø 0.2 mm)

Connection



Electrical connection - socket

Connector: 1 x valve type B DIN, angled; Moulded body: PUR; Locking: stainless steel (1.4404 / 316L)

