
E20408

Fibre optic diffuse reflection sensor

FT-30-A-A-M8/1,2M

Article no longer available - archive entry



Application		
Function principle		Diffuse reflection sensor
Detection zone		
Range with fibre optic amplifier type		OIF
OIF		
Range fibre optics	[mm]	70
Operating conditions		
Ambient temperature	[°C]	-40...290
Mechanical data		
Version of sensing head		straight
Sensing head thread		M8
Total length	[mm]	1200
Min. bending radius	[mm]	30
Materials		Adapter: PA
Fibre material		glass
Fibre head material		aluminium
Fibre sheath material		aluminium

E20408

Fibre optic diffuse reflection sensor

FT-30-A-A-M8/1,2M

Remarks	
Pack quantity	1 pcs.