
E33112

Mounting adapter for process sensors

ADAPT IFM-CHERRY-BURELL 2

Article no longer available - archive entry



1 Aseptoflex thread
2 Aseptoflex sealing edge

Application		
Pressure rating	[bar]	25
Mechanical data		
Materials		stainless steel (1.4404 / 316L)
Sensor connection		Aseptoflex
Process connection		flange 2"
Surface characteristics Ra/Rz of the wetted parts		0.4 / 4
Hygienic equipment class to DIN 11866		H4
Remarks		
Pack quantity		1 pcs.