
SI8518

Flow monitor

KIT, SI0508 W/ E40107



Product characteristics		
Number of inputs and outputs		Number of digital outputs: 1
Process connection		M18 x 1,5 internal thread
Application		
Media		Liquids; Gases
Medium temperature	[°C]	-25...80
Pressure rating	[bar]	30
Liquids		
Medium temperature	[°C]	-25...80
Gases		
Medium temperature	[°C]	-25...80
Electrical data		
Operating voltage	[V]	20...36 DC; (according to EN 50178 SELV/PELV ; with reference to UL: "limited voltage" with overcurrent protection in accordance with UL508)
Current consumption	[mA]	< 80

SI8518

Flow monitor

KIT, SI0508 W/ E40107

Reverse polarity protection			yes
Power-on delay time	[s]		10; (optically indicated)
Inputs / outputs			
Number of inputs and outputs			Number of digital outputs: 1
Outputs			
Total number of outputs			1
Output signal			switching signal
Electrical design			PNP
Number of digital outputs			1
Output function			normally open / normally closed; (parameterisable)
Max. voltage drop switching output DC	[V]		2.5
Permanent current rating of switching output DC	[mA]		400
Short-circuit protection			yes
Type of short-circuit protection			pulsed
Overload protection			yes
Measuring/setting range			
Probe length L	[mm]		45
Liquids			
Setting range	[cm/s]		3...300
Greatest sensitivity	[cm/s]		3...60
Gases			
Setting range	[cm/s]		200...3000
Greatest sensitivity	[cm/s]		200...800
Response times			
Response time	[s]		1...10
Liquids			
Response time	[s]		1...10
Gases			
Response time	[s]		1...10
Software / programming			
Adjustment of the switch point			+/- pushbutton
Operating conditions			
Ambient temperature	[°C]		-25...80
Protection			IP 67
Tests / approvals			
Shock resistance		DIN IEC 68-2-27	50 g (11 ms)
Vibration resistance		DIN EN 60068-2-6	20 g (55...2000 Hz)
Mechanical data			
Weight	[g]		326.586
Dimensions	[mm]		M18 x 1.5

SI8518

Flow monitor

KIT, SI0508 W/ E40107

Thread designation	M18 x 1.5	
Materials	PBT-GF20	
Materials (wetted parts)	stainless steel (1.4404 / 316L); O-ring: FKM 80 Shore A	
Process connection	M18 x 1,5 internal thread	
Displays / operating elements		
Display	function	10 x LED, three-colour
Accessories		
Items supplied	Adapter: 1 x 1/2-14NPT, E40107	
Remarks		
Pack quantity	1 pcs.	
Electrical connection		

Connector: 1 x M12; coding: A



Connection

