
E11252

Wirable socket

SDOAH040VASFKPG



Application		
Special feature		Free from silicone; Gold-plated contacts
Free from silicone		yes
Electrical data		
Operating voltage	[V]	< 45 AC / < 70 DC
Max. current load total	[A]	4; (...40 °C)
Operating conditions		
Ambient temperature	[°C]	-40...85
Protection		IP 68
Mechanical data		
Weight	[g]	28.2
Dimensions	[mm]	39 x 19 x 31
Materials		PBT
Moulded-body material		PBT
Material nut		stainless steel (1.4404 / 316L)
Remarks		
Pack quantity		1 pcs.

E11252

Wirable socket

SDOAH040VASFKPG

Electrical connection

screw terminals: ...0.75 mm²; Cable sheath: Ø 6...8 mm

Electrical connection - socket

Connector: 1 x M12, angled; coding: A; Moulded body: PBT; Locking: stainless steel (1.4404 / 316L); Contacts: gold-plated



Connection

