
E20415

Fibre optic diffuse reflection sensor

FT-00-P-V-E2,5/0,8M

Article no longer available - archive entry



Application		
Function principle		Diffuse reflection sensor
Detection zone		
Range with fibre optic amplifier type		OKF; OUF
OKF		
Range fibre optics	[mm]	4
OUF		
Range fibre optics	[mm]	4
Operating conditions		
Ambient temperature	[°C]	-20...80
Mechanical data		
Version of sensing head		straight
Sensing head diameter	[mm]	2.4
Total length	[mm]	800
Materials		Adapter: PPE
Fibre material		glass
Fibre head material		stainless steel (1.4305 / 303)
Fibre sheath material		PVC
Remarks		
Pack quantity		1 pcs.