
E70143

Jumper cable with valve plug

VVDAB031--S00,3A03STAH030VAS



Application			
Special feature			Halogen-free
Electrical data			
Operating voltage	[V]		< 24 AC/DC
Operating conditions			
Ambient temperature	[°C]		-25...90
Protection			IP 67
Mechanical data			
Weight	[g]		58.7
Dimensions	[mm]		30 x 15 x 39
Materials			PUR
Moulded-body material			PUR
Material nut			stainless steel (1.4404 / 316L)
Displays / operating elements			
Display		switching status	1 x LED, yellow
Accessories			
Items supplied			screw
			panel for labelling

E70143

Jumper cable with valve plug


VVDAB031--S00,3A03STAH030VAS

Remarks

Pack quantity	1 pcs.

Electrical connection - plug


Connector: 1 x M12, angled; coding: A; Moulded body: PUR; Locking: stainless steel (1.4404 / 316L)



Electrical connection

Cable: 0.3 m, PUR, Halogen-free, black, Ø 5.5 mm; 3 x 0.5 mm² (16 x Ø 0.2 mm)

Connection



Electrical connection - socket

Connector: 1 x valve type B DIN, angled; Moulded body: PUR; Locking: stainless steel (1.4404 / 316L)

