# E33032

## Process adapter for SMS pipe fitting


ADAPT IFM-SMS DN50 (2)

phase-out article

Alternative articles: E33732

When selecting an alternative article and accessories please note that technical data may differ!

The alternative article requires the use of a new sensor with Aseptoflex Vario external thread




1 Aseptoflex thread
2 Aseptoflex sealing edge

EC 1935/2004 FDA

| | | |
|---|---|---|
| **Application** | | |
| Pressure rating | [bar] | 25 |
| **Tests / approvals** | | |
| Pressure Equipment Directive | | A possible classification to PED depends on the application and has to be carried out by the user / operator. |
| Safety instructions | | The compatibility between medium and product material has to be checked in all applications. |
| **Mechanical data** | | |
| Weight | [g] | 273.8 |
| Materials | | stainless steel (1.4404 / 316L) |
| Sensor connection | | Aseptoflex |
| Process connection | | SMS pipe fitting DN50 (2") |
| Surface characteristics Ra/Rz of the wetted parts | | 0.4 / 4 |
| Hygienic equipment class to DIN 11866 | | H4 |
| **Remarks** | | |
| Pack quantity | | 1 pcs. |