
E34010

Thermowell for temperature sensors

HYGIENIC THERMOWELL L=100

Article no longer available - archive entry



1 Aseptoflex thread

3A EC 1935/2004 EHEDG Tested FDA

Application		
Design		for temperature sensors Ø 10 mm
Pressure rating	[bar]	25
Measuring/setting range		
Probe length L	[mm]	95
Mechanical data		
Weight	[g]	194
Materials		stainless steel (1.4404 / 316L)
Sensor connection		G 1/2 Ø 10 mm
Process connection		Aseptoflex
Surface characteristics Ra/Rz of the wetted parts		< 0.6 / -
Remarks		
Pack quantity		1 pcs.