
E7377A

AS-Interface flat cable splitter

FC Splitter ye/ye II 3D/3G



CE

Application		
Application		for the distribution of the AS-i voltage or the external 24 V supply
Electrical data		
Protection class		III
Max. current load total	[A]	8
Outputs		
Electrical design		AS-i
Operating conditions		
Ambient temperature	[°C]	0...60
Protection		IP 67; (when used outside the hazardous area: IP 68 / IP 69K)
Tests / approvals		
ATEX marking		II 3G Ex nA II T6 Gc X
		II 3D Ex tc IIIC T 70°C Dc X
Mechanical data		
Weight	[g]	132.5
Materials		metal parts: stainless steel (1.4404 / 316L); rubber gasket for contact pins: FKM; Sealing: EPDM
Tightening torque	[Nm]	2.5; (Mounting screw)
Accessories		
Accessories (optional)		Torque wrench:, E70390
		flat cable blank:, E70299
Remarks		
Pack quantity		1 pcs.