
E80353

RFID tag

ID-TAG/R30X10/04



Application		
Operating temperature (active)	[°C]	-25...85
Peak temperature (passive)	[°C]	100
Electrical data		
Operating frequency	[MHz]	865...870
Memory size	[bit]	128
Max. read cycles		unlimited
Max. write cycles		100000
Operating conditions		
Ambient temperature	[°C]	-25...85
Storage temperature	[°C]	-40...100
Mechanical data		
Weight	[g]	8.2
Dimensions	[mm]	Ø 30 / L = 10
Materials		PU black
Remarks		
Pack quantity		1 pcs.
Other data		

read distance (m)

DTE80x	0.5
DTE90x	-
ANT860 / ANT960	-
ANT820 / ANT920	-