
EC2100

CAN bus test unit

R360/CAN BusTester

Article no longer available - archive entry



CE

Product characteristics		
Image resolution	[px]	800 x 480
Electrical data		
Operating voltage	[V]	10...32 DC
Detection zone		
Image resolution	[px]	800 x 480
Interfaces		
Number of CAN interfaces		1
Number of Ethernet interfaces		1
Number of USB interfaces		2
Operating conditions		
Storage temperature	[°C]	-10...60
Protection		IP 62
Mechanical data		
Weight	[g]	1483.5

EC2100

CAN bus test unit

R360/CAN BusTester

Dimensions	[mm]	178 x 199 x 67	
Materials		plastics: ABS	
Displays / operating elements			
Display			7" colour display
Operating elements			pushbuttons
			touch screen
Display type		colour display	
Display size		7"	
Display background illumination		LED	
Remarks			
Pack quantity		1 pcs.	
Electrical connection			
Connector: 1 x M12			