
E11089

Connecting cable with socket

ADOAF030VAS0005E03

Article no longer available - archive entry




Electrical data		
Operating voltage	[V]	< 60 AC / < 75 DC
Protection class		III
Operating conditions		
Ambient temperature	[°C]	-25...90
Protection		IP 67
Mechanical data		
Dimensions	[mm]	17 x 10 x 26
Materials		TPU
Moulded-body material		TPU
Material nut		stainless steel (1.4305 / 303)
Remarks		
Pack quantity		1 pcs.

Electrical connection

Cable: 5 m, PVC, orange, Ø 5 mm; 3 x 0.34 mm² (42 x Ø 0.1 mm)

Electrical connection - socket

Connector: 1 x M8, angled; coding: A; Moulded body: TPU; Locking: stainless steel (1.4305 / 303)




E11089

Connecting cable with socket

ADOAF030VAS0005E03

Connection



	Core colours :
BN =	brown
BK =	black
BU =	blue