
E20298

Fibre optic diffuse reflection sensor

FT-30-P-V-M8

Article no longer available - archive entry

Alternative articles: E20156
When selecting an alternative article and accessories please note that technical data may differ!



Application		
Function principle		Diffuse reflection sensor
Detection zone		
Range with fibre optic amplifier type		OIF
OIF		
Range fibre optics	[mm]	70
Operating conditions		
Ambient temperature	[°C]	-20...80
Mechanical data		
Version of sensing head		straight
Sensing head thread		M8
Total length	[mm]	600
Min. bending radius	[mm]	30
Materials		Adapter: PA
Fibre material		glass
Fibre head material		stainless steel (1.4305 / 303)

E20298

Fibre optic diffuse reflection sensor

FT-30-P-V-M8

Fibre sheath material	PVC

Remarks	
Pack quantity	1 pcs.