
E10971

Connecting cable with socket

ADOAF032VAS0020E03

Article no longer available - archive entry



Electrical data		
Operating voltage	[V]	10...30 DC
Outputs		
Electrical design		PNP
Operating conditions		
Ambient temperature	[°C]	-25...90
Protection		IP 67
Mechanical data		
Materials		TPU transparent
Moulded-body material		TPU, transparent
Material nut		stainless steel (1.4404 / 316L)
Displays / operating elements		
Display	switching status	1 x LED, yellow
	operation	1 x LED, green
Remarks		
Pack quantity		1 pcs.

E10971

Connecting cable with socket


ADOAF032VAS0020E03

Electrical connection


Cable: 20 m, PVC, orange, Ø 5 mm; 3 x 0.34 mm²

Electrical connection - socket

Connector: 1 x M8, angled; coding: A; Moulded body: TPU, transparent; Locking: stainless steel (1.4404 / 316L)



Connection



	Core colours :
BN =	brown
BK =	black
BU =	blue