
# E70189

## Connection cable

VDOGH040VAS0010E04STGH040VAS

Article no longer available - archive entry




| | | |
|---|---|---|
| **Application** | | |
| Special feature | | Free from silicone; Gold-plated contacts |
| Free from silicone | | yes |
| **Electrical data** | | |
| Operating voltage | [V] | < 250 AC / < 300 DC |
| Max. current load total | [A] | 4 |
| **Operating conditions** | | |
| Ambient temperature | [°C] | -25...100 |
| Protection | | IP 68; IP 69K |
| **Mechanical data** | | |
| Materials | | PVC |
| Moulded-body material | | PVC |
| Material nut | | stainless steel (1.4404 / 316L) |
| **Remarks** | | |
| Pack quantity | | 1 pcs. |

# E70189

## Connection cable

VDOGH040VAS0010E04STGH040VAS

### Electrical connection - plug


Connector: 1 x M12, straight; coding: A; Moulded body: PVC; Locking: stainless steel (1.4404 / 316L); Contacts: gold-plated; Tightening torque: 0.7...0.9 Nm




### Electrical connection

Cable: 10 m, PVC, orange, Ø 5.3 mm; 4 x 0.34 mm² (42 x Ø 0.1 mm )

Connection




### Electrical connection - socket

Connector: 1 x M12, straight; coding: A; Moulded body: PVC; Locking: stainless steel (1.4404 / 316L); Contacts: gold-plated; Tightening torque: 0.7...0.9 Nm

