
E37511

Thermowell for temperature sensors

THERMOWELL, D6/ G1/2 conical/L=100



EC 1935/2004 EHEDG Tested FDA

Application		
Design		for temperature sensors EL = 100 mm
Pressure rating	[bar]	16
Mechanical data		
Weight	[g]	184.55
Materials		stainless steel (1.4404 / 316L)
Sensor connection		G 1/2 sealing cone Ø 6 mm
Process connection		G 1/2
Surface characteristics Ra/Rz of the wetted parts		≤ 0.6 / -
Installation length EL	[mm]	68
Bore length BL	[mm]	137
Remarks		
Pack quantity		1 pcs.